




2022 ISC SECTIONALS WOMEN'S SINGLES



DISTANCE:	39 FEET	VOLUME:	26.685 mL
RATIO:	2.44:1	FORWARD:	17.235 mL
DROP BRUSH:	38 FEET	REVERSE:	9.45 mL
TANKS: CURRENT & CURRENT		PUMP:	45µL



FORWARD LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	BUFF	TANK	DISTANCE	T.OIL
1	2L	2R	6	45	18	3	A - Current	0 → 13	9,990
2	6L	6R	1	45	18	3	A - Current	13 → 15	1,305
3	7L	7R	1	45	18	3	A - Current	15 → 18	1,215
4	8L	8R	1	45	18	3	A - Current	18 → 20	1,125
5	9L	9R	1	45	18	3	A - Current	20 → 23	1,035
6	10L	10R	1	45	18	3	A - Current	23 → 25	945
7	11L	11R	1	45	18	3	A - Current	25 → 28	855
8	12L	12R	1	45	18	3	A - Current	28 → 30	765
9	2L	2R	0	45	18	3	A - Current	30 → 34	0
10	2L	2R	0	45	22	3	A - Current	34 → 39	0


REVERSE LOADS DATA

#	START	STOP	LOADS	MICS	SPEED	BUFF	TANK	DISTANCE	T.OIL
1	2L	2R	0	45	30	3	B - Current	38 → 26	0
2	11L	11R	1	45	26	3	B - Current	26 → 22	855
3	10L	10R	1	45	22	3	B - Current	22 → 19	945
4	9L	9R	1	45	18	3	B - Current	19 → 17	1,035
5	8L	8R	1	45	18	3	B - Current	17 → 14	1,125
6	7L	7R	2	45	14	3	B - Current	14 → 10	2,430
7	5L	5R	1	45	14	3	B - Current	10 → 8	1,395
8	2L	2R	1	45	14	3	B - Current	8 → 6	1,665
9	2L	2R	0	45	14	3	B - Current	6 → 0	0

THIS PATTERN IS DESIGNED FOR:

DUAL CONDITIONING TANKS | REVERSE DROP BRUSH

This pattern may require adjustments if using a lane machine that does not have these features



SCAN QR CODE TO
SHARE AND
DOWNLOAD
THIS PATTERN



KEGEL PATTERN LIBRARY APP



PATTERNLIBRARY.KEGEL.NET