




# 2010 EBT BOWLTECH AALBORG INTERNATIONAL - LEFT LANE



|                    |                |                 |                |
|--------------------|----------------|-----------------|----------------|
| <b>DISTANCE:</b>   | <b>42 FEET</b> | <b>VOLUME:</b>  | <b>23.4 mL</b> |
| <b>RATIO:</b>      | <b>2.97:1</b>  | <b>FORWARD:</b> | <b>11.2 mL</b> |
| <b>DROP BRUSH:</b> | <b>42 FEET</b> | <b>REVERSE:</b> | <b>12.2 mL</b> |
| <b>TANKS:</b>      | <b>KEGEL</b>   | <b>PUMP:</b>    | <b>50µL</b>    |




## FORWARD LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 3     | 50   | 14    | 3    | A - Kegel | 0 → 4    | 5,550 |
| 2 | 7L    | 7R   | 1     | 50   | 14    | 3    | A - Kegel | 4 → 6    | 1,350 |
| 3 | 10L   | 9R   | 1     | 50   | 14    | 3    | A - Kegel | 6 → 8    | 1,100 |
| 4 | 12L   | 10R  | 2     | 50   | 14    | 3    | A - Kegel | 8 → 12   | 1,900 |
| 5 | 14L   | 12R  | 1     | 50   | 14    | 3    | A - Kegel | 12 → 14  | 750   |
| 6 | 16L   | 14R  | 1     | 50   | 18    | 3    | A - Kegel | 14 → 16  | 550   |
| 7 | 2L    | 2R   | 0     | 50   | 18    | 3    | A - Kegel | 16 → 27  | 0     |
| 8 | 2L    | 2R   | 0     | 50   | 22    | 3    | A - Kegel | 27 → 34  | 0     |
| 9 | 2L    | 2R   | 0     | 50   | 26    | 3    | A - Kegel | 34 → 42  | 0     |

## REVERSE LOADS DATA

| # | START | STOP | LOADS | MICS | SPEED | BUFF | TANK      | DISTANCE | T.OIL |
|---|-------|------|-------|------|-------|------|-----------|----------|-------|
| 1 | 2L    | 2R   | 0     | 50   | 30    | 3    | A - Kegel | 42 → 32  | 0     |
| 2 | 15L   | 13R  | 1     | 50   | 22    | 3    | A - Kegel | 32 → 29  | 650   |
| 3 | 13L   | 12R  | 2     | 50   | 18    | 3    | A - Kegel | 29 → 24  | 1,600 |
| 4 | 11L   | 11R  | 2     | 50   | 18    | 3    | A - Kegel | 24 → 19  | 1,900 |
| 5 | 9L    | 9R   | 1     | 50   | 18    | 3    | A - Kegel | 19 → 16  | 1,150 |
| 6 | 7L    | 7R   | 1     | 50   | 14    | 3    | A - Kegel | 16 → 14  | 1,350 |
| 7 | 2L    | 2R   | 3     | 50   | 14    | 3    | A - Kegel | 14 → 8   | 5,550 |
| 8 | 2L    | 2R   | 0     | 50   | 14    | 3    | A - Kegel | 8 → 0    | 0     |



KEGEL PATTERN LIBRARY APP



PATTERNLIBRARY.KEGEL.NET



SCAN QR CODE TO  
SHARE AND  
DOWNLOAD  
THIS PATTERN

